



Winkonlaser
Bringing Beauty and Love by Technology

Add: D2510, Victoria Building, Beijing, China

WhatsApp: +8618533632296

Email: info@winkonlaser.com

Web: www.winkonlaser.com/www.beautemax.com

Winkonlaser®


Bringing Beauty and Love by Technology

DIODE LASER

Stronger

Faster

Smarter



Introducing DL1500

Featuring its exclusive 3D technology, DL1500 combines the three most effective laser wavelengths into a single applicator, simultaneously targeting different tissue depths and anatomical structures within the hair follicle. By combining the absorption and penetration levels of different wavelengths, along with extended treatment coverage, increased comfort and low maintenance requirements.



The DL1500 System Highlights



Exceptionally Large Spot Size Quick and Comfortable

A unique and efficient 3D new applicator with an especially large spot size of 4.8cm, for faster treatments and better patient experience.



ICE Plus Continuous Contact Cooling

DL1500 especially equipped with a Hitachi imported compressor refrigeration, ensure that the machine has a continuous contact cooling system and machine can achieve 24 hours continuous work normally and stably.



Dual Connector More Flexibility

DL1500 is the first version of Soprano hair removal systems that includes two connectors, which enables two different applicators to be connected to the platform at all times.



15'4 4K HD Screen Friendly and Functional


Equipped with a new large sized 15'6 Android screen, with pre-set parameters, practitioners can enjoy a more intuitive, user friendly work experience.





Synergetic Technologies. Superior Results.

DL1500 proprietary hair removal innovation is the only clinically proven method of laser hair removal that is virtually painless, and it is the safest laser hair removal method for all skin types, including dark and tanned skin. Its unique gradual heating and rapid/fast pulse delivery method effectively damages the hair follicle and hinders re-growth, while preventing injury to the surrounding tissue. It affects the melanin of the skin using a unique method, allowing the procedure to be performed on all skin types anytime of the year as well as on tanned skin.



ALEX
755nm

The Alexandrite wavelength improves the absorption of powerful energy by the melanin chromophore, making it ideal for the most extensive range of hair colors and types, especially light-colored and thin hair. With increased superficial penetration, the 755nm wavelength targets the Bulge of the hair follicle and is especially effective for superficially embedded hair in areas such as the eyebrows and upper lip.

SPEED
808nm

The 808nm is a classic hair removal wavelength, offering deep penetration of the hair follicle with high average power, and a rapid repetition rate and a large 2cm. spot size for time-efficient treatments. The 810nm has a moderate melanin absorption level, making it safe for darker skin types. Its deep penetration capabilities target the Bulge and Bulb of the hair follicle, while moderate tissue depth penetration makes it ideal for treating the arms, legs, cheek and chin.

SPECIAL
940nm

The 940nm wavelength mainly arrived dermis layer, it is better for vascular removal and skin rejuvenation and better for removing hair with colors other than black.

YAG
1064nm

The YAG 1064 wavelength is characterized by lower melanin absorption, making it a perfect solution for darker skin types. The 1064nm also offers the deepest penetration of the hair follicle, so that it targets the Bulb and Papilla, while deeply treating embedded hair in areas such as the scalp, armpits and pubic areas. With higher water absorption generating a higher temperature, incorporating the 1064nm wavelength increases the thermal profile of the overall treatment, leading to highly effective hair removal and improved results.



Leveraging Larger Spot Size 12*40mm

This exclusive applicator is a valuable asset for any clinic. With its large spot size **4.8cm**, and integration of three wavelengths, it facilitates increased treatment coverage to significantly reduce treatment time and make the process easier and more comfortable for patients. With Quattro, hair removal is quick, efficient and convenient.



The bars we used is imported from **German JENOPTIK Laser GmbH** company, the world's top diode laser manufacturer.

Single palladium bar power exceeds **120W**

Longer lifetime: **100 million time shots.**

TRIO one 14*25mm Three in One

This applicator enables the delivery of three highly effective wavelengths in one. Covering a spot size, it simultaneously targets different tissue depths and anatomical structures within the hair follicle, increasing treatment efficiency.



Small 4mm spot size for options. It can be used for very small places hair removal, such as ears,nose .

Platform Benefits

- * LARGE SPOT SIZE FOR QUICK TREATMENTS
 - * ICE PLUS™ CONTINUOUS COOLING SYSTEM
 - * TWO CONNECTORS
 - * CLINICALLY PROVEN 3D TECHNOLOGY
 - * INTUITIVE, USER FRIENDLY LARGE SCREEN (15.4" ANDROID) WITH PRE-SET PARAMETERS
 - * I-VI SKIN TONES AND TANNED SKIN
 - * NO CONSUMABLES
-

